

Artículo/Article		<b>SARGA CANIGO TECNOSANI</b>		<b>MASK FFP2 (test itel CE-11340)</b>	
REUSABLE (>25 washes)		MADE IN SPAIN		TESTED (ACCORDING UNE-EN14683 and UNE-006 CEE/93/42)	
<b>ANÁLISIS FÍSICO / PHYSICAL ANALYSIS</b>					
CARACTERÍSTICAS		RESULTADOS / RESULTS		VALORES / VALUES	
TEST					
Nº de Hilo/Thread Count	Urdimbre / Warp		20 1/C		
	Trama / Weft		20 1/C		
Densidad / Density	Urdimbre / Warp		96		
	Trama / Weft		57		
Ligamento / Weave		SARGA 2/1 S / TWILL 2/1 S			
Comp. Urd./ Comp. Warp		35% COTTON / 65% PES			ISO 1833:2006
Comp. Tr./ Comp.Weft		35% COTTON / 65% PES			
Total Comp.		35% COTTON / 65% PES			Simple: No tolerancia Compuesta: +/- 3%
Ancho Final / Final Width		cm	160		+/-2% ISO 3932:1976
Peso / Weight		gr/m <sup>2</sup>	195 - 205		+/-5% ISO 3801:1977
Resistencia Rotura/ Breakage	(Kgs.)	Urdimbre		pass	kgf EN-13795
		Trama		pass	kgf
Resistencia Abrasion		pass			EN-13795
Resistencia Desgarro / Tear		Urdimbre/Warp (G)	N/A	Trama / Weft	N/A EN-13795
Encogimiento / Shrinkage	°C	60	% Urdimbre		+/- 2
			% Trama		
				<b>0 - 3 %</b>	NP EN ISO 5077:2008
<b>SPECIAL MEDICAL TESTS</b>					
CARACTERÍSTICAS		RESULTADOS / RESULTS		VALORES / VALUES	
TEST					
Washing solidity 60°C		5		0-5 UNE EN ISO-05	
Pilling		5		0-5 UNE EN ISO 12945-2	
Traspirability		< 60 Pa/cm <sup>2</sup>		AST1	
Aerosol Filtration Efficiency		>94%		UNE EN14683	
Particle Filtration Efficiency		>94%		UNE EN14683	
Particle Filtration		0,4 micras and >96% efficiency		UNE EN149	
Bacterial presence		DRY: PASS	WET: PASS	EN-13795	
<b>ANÁLISIS QUÍMICO / CHEMICAL ANALYSIS</b>					
CARACTERÍSTICAS		RESULTADOS / RESULTS		VALORES / VALUES	
TEST					
pH		Conforme/According Oeko-Tex II		4,0 - 7,5 UNI EN ISO 3071/06	
Formaldehído		Conforme/According Oeko-Tex II		<16ppm   < <b>75ppm</b> UNE EN ISO 14184-1:1999	
Arlaminas		Conforme/According Oeko-Tex II		<b>20 ppm</b> UNE 2002/61/CE	
<b>PROHIBIDOS / FORBIDDEN</b>					
Metales Pesados		Conforme/According Oeko-Tex II		Niquel 0,5 Pg/cm <sup>2</sup> - Cadmio 75 pm - Plomo 100 ppm	
AZO Colorants		Conforme/According Oeko-Tex II		No detectable	
Colorantes Alérgicos		Conforme/According Oeko-Tex II		No detectable (LMBG) (1/4/96)	
SÍMBOLOS DE LAVADO / WASH CARE SYMBOLS					
<b>Observaciones:</b>					
<b>TRAS 25 LAVADOS EL ACABADO EMPIEZA A PERDER PROPIEDADES - LAVAR CON DETERGENTE NEUTRO</b>					
AFTER 25 WASHES THE FINISH BEGINS TO LOSE PROPERTIES - WASH WITH NEUTRAL DETERGENT					
NO USAR LEJIA / DO NOT USE BLEACHING					
PLANCHADO A 140° de 10-15 SEGUNDOS / IRON 140° FOR 10-15 SECONDS					
GRS POST CONSUME bajo pedido / on request					